

M52 x 0.75 Mounted UV/IR Cut-Off Filter



Stock **#54-750** 10 TO 12 DAYS

⊖ 1 ⊕

₹19,575.00

ADD TO CART

Qty 1-9
₹19,575.00
Qty 10+
₹18,018.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
52.8

Filter Thread:
M52 x 0.75

Cut-Off Wavelength (nm):
690.00

Cut-On Wavelength (nm):
390.00

Index of Refraction n_d: 1.52 Substrate, Varies by Layer
Note: AR Coating: Both Surfaces Multi-Layer
Outer Diameter (mm): 54.0
Substrate: ☐ Float Glass
Substrate Thickness (mm): 2.0
Surface Quality: 60-40
Thickness with Mount (mm): 7.0
Type: Mounted Imaging Filter

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant