

[See all 4 Products in Family](#)

M6 x 1.0 Bumper (Package of 4), Sorbothane Bumpers



Stock #56-923 **20+ In Stock**

- 1 + MRP ₹4,869

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-2	₹4,869 each
Qty 3+	₹4,318 each
Need More?	Request Quote

Product Downloads

General

Metric **Type:**
Thread Type: M6 **Note:**

Physical & Mechanical Properties

Thickness (mm):

25.40

Construction:

Sorbothane

Diameter (mm):

38.10

Load Capacity (lbs):

30-65 / bumper

Threading & Mounting

Thread Length (mm):

12.7

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Reach 211:

[Compliant](#)

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Absorb and Dissipate Vibration
- Stabilize Equipment up to 152lbs
- English, Metric, or Universal Styles

Sorbothane® Mounts absorb (57% absorption efficiency) and dissipate energy (70% specific damping). The mounts reduce vibration to other components by isolating the vibrations within the material while absorbing multi-directional forces. These hemisphere mounts can stabilize equipment weighing up to 38 pounds (hemisphere mounts), 65 pounds (1/4-20 male bumper mounts), or 29.4 kg (M6 male bumper mounts). Sorbothane® Mounts measure 50mm dia. (top) x 26mm thick. The top side of the hemisphere is tacky, while the other side is felt. 1/4-20 or M6 male bumper mounts measure 38.1mm dia. x 25.4mm thick. The threaded screw measures 12mm long. All models have a hardness durometer value of 70. Each package contains 4 mounts.