

[See all 9 Products in Family](#)

M34.0 x 0.50 1.5mm Thick, Uncoated, Machine Vision Mounted Sapphire Window



Machine Vision Mounted Sapphire Windows

Stock #23-283 **2 In Stock**

MRP ₹18,160

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹18,160 each
Qty 10-24	₹16,344 each
Qty 25+	₹15,537 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**

Physical & Mechanical Properties

28.44 **Clear Aperture CA (mm):**

Diameter (mm):

31.60 +0/-0.20

1.50 ±0.10 **Thickness (mm):**

≤3.5 **Parallelism (arcmin):**

Protective as needed **Bevel:**

≥90 **Clear Aperture (%):**

Fine Ground **Edges:**

0.27 **Poisson's Ratio:**

435 **Young's Modulus (GPa):**

1,900.00 **Knoop Hardness (kg/mm²):**

Optical Properties

Uncoated **Coating:**

Sapphire (Al₂O₃) **Substrate:**

1.77 **Index of Refraction (n_d):**

80-50 **Surface Quality:**

72.24 **Abbe Number (v_d):**

0.008 for Visible Light Orthogonal to Optical Axis **Birefringence (n_o-n_e):**

Random **Axis Orientation:**

330 - 5500 **Wavelength Range (nm):**

2λ (typical) **Surface Flatness (P-V):**

Threading & Mounting

M34.0 x 0.50 **Filter Thread:**

36.00 **Mount Diameter (mm):**

6.5 **Mount Thickness (mm):**

Material Properties

3.97 **Density (g/cm³):**

8.8 **Coefficient of Thermal Expansion CTE (10⁻⁶/°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Switzerland **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- Protective Windows for Machine Vision Applications
- Windows Feature Extreme Surface Hardness and Chemical Resistance
- M25.5 to M62.0 Filter Threads Available

Machine Vision Mounted Sapphire Windows are mounted in durable anodized aluminum housings with common filter threads for easy integration with most imaging lenses. The windows within the mount are manufactured from durable sapphire making them ideal for rugged environments because of their extreme surface hardness, high thermal conductivity, high dielectric constant and resistance to common chemical acids and alkalis. Machine Vision Mounted Sapphire Windows feature both male and female threads, allowing them to be combined with other mounted filters or polarizers. The uncoated windows are useful within a transmission range from 330 – 550nm making them ideal for machine vision applications in the UV, Visible, and Infrared spectra.

