

## Medium Thick Base Single Movement



#03-681

Stock **#03-681** **3 In Stock**

⊖ 1 ⊕ ₹16,577

**ADD TO CART**

### Volume Pricing

Qty 1-9	₹16,577 each
Qty 10+	₹14,633 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

English **Type:**

Not Lockable **Note:**

### Physical & Mechanical Properties

Linear (X) **Type of Movement:**

**Guide System:**

Dovetail	
20 x 100	<b>Stage Size (mm):</b>
40 (±20)	<b>Travel (mm):</b>
3.5 Horizontal, 2.1 Vertical	<b>Load Capacity (kg):</b>
50	<b>Straight Line Accuracy (µm):</b>
15	<b>Travel Per Knob Rotation (mm):</b>
422	<b>Weight (g):</b>
20 x 60	<b>Table Size (mm):</b>

## Hardware & Interface Connectivity

Rack and Pinion	<b>Type of Drive:</b>
-----------------	-----------------------

## Threading & Mounting

Stage: (1) 1/4-20 Base: (3) 1/4-20	<b>Mounting Threads:</b>
---------------------------------------	--------------------------

## Regulatory Compliance

<a href="#">Exempt</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Contains SVHC(s)</a>	<b>Reach 235:</b>
Japan	<b>Country of Origin:</b>
Edmund Optics India Private Limited	<b>Importer:</b>

## Product Details

- Multiple Configurations Available
- High Load Capacity
- Ideal for Applications Requiring Long Travel
- Additional [Rack and Pinion Stages](#) Available

Basic Rack and Pinion Stages are ideal for applications requiring high load capacity or long travel. These stages feature horizontal load capacities of 3.5kg and vertical load capacities of 2.1kg. Each stage offers stage and base mounting holes and features steel construction with brass movement. Basic Rack and Pinion Stages are available in multiple configurations with varying stage sizes. These stages have a Dovetail guide system.

## Technical Information

