

Mounted M22.5 x 0.5 - UV Cut-Off Filter



Mounted UV Filters

Stock **#58-647** **2 In Stock**

-

1

+

₹6,929

ADD TO CART

Volume Pricing	
Qty 1-9	₹6,929 each
Qty 10+	₹6,582 each
Need More?	Request Quote

Product Downloads

General

Type:

Mounted Imaging Filter

Physical & Mechanical Properties

Clear Aperture CA (mm):

18.5

Outer Diameter (mm):

24.0

Thickness with Mount (mm):

5.00	
Thickness (mm):	2.00 ±0.2
Substrate Thickness (mm):	2.5
Optical Properties	
Cut-On Wavelength (nm):	390.00
Glass/Filter Number:	L-39
Substrate: ☐	Hoya L-39
Coating:	Uncoated
Color:	Clear
Surface Quality:	80-50
Wavelength Range (nm):	350 - 2200
Surface Flatness (P-V):	4 - 6λ
Threading & Mounting	
Filter Thread:	M22.5 x0.50
Mount Thickness (mm):	5.2 ±0.3
Mount Thickness Including Threads (mm):	7
Environmental & Durability Factors	
Operating Temperature (°C):	-15 to +70
Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 242:	Compliant
Country of Origin:	United States
Importer:	Edmund Optics India Private Limited

Product Details

- Blocks UV and Transmits Visible
 - Ideal as Dust or Protective Covers for Camera Sensors
- Mounted UV Filters are offered with standard photographic and lens filter mount threads. These filters are ideal for applications where UV light needs to be blocked and visible light passed. The mounted clear aperture is 5mm less than the mount diameter. The maximum outer diameter is 2mm greater than the mount diameter, except for the 62mm and 72mm, which are 3mm larger. Mounted UV Filters are clear in color and non-rotatable.

Technical Information



