

Mounted M25.5 x 0.5 - UV Cut-Off Filter



Mounted UV Filters

Stock #46-577 **5 In Stock**

1
MRP ₹10,493

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹10,493 each
Qty 10+	₹9,989 each
Need More?	Request Quote

Product Downloads

General

Mounted Imaging Filter Type:

Physical & Mechanical Properties

21.0 Clear Aperture CA (mm):

27.5 Outer Diameter (mm):

7.00	Thickness with Mount (mm):
2.00 ±0.2	Thickness (mm):
2.5	Substrate Thickness (mm):

Optical Properties

390.00	Cut-On Wavelength (nm):
L-39	Glass/Filter Number:
Hoya L-39	Substrate: <input type="checkbox"/>
Uncoated	Coating:
Clear	Color:
80-50	Surface Quality:
350 - 2200	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):

Threading & Mounting

M25.5 x 0.50	Filter Thread:
5.2 ±0.3	Mount Thickness (mm):
7	Mount Thickness Including Threads (mm):

Environmental & Durability Factors

-15 to +70	Operating Temperature (°C):
------------	------------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:
United States	Country of Origin:
Imported By:	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- Blocks UV and Transmits Visible
- Ideal as Dust or Protective Covers for Camera Sensors

Mounted UV Filters are offered with standard photographic and lens filter mount threads. These filters are ideal for applications where UV light needs to be blocked and visible light passed. The mounted clear aperture is 5mm less than the mount diameter. The maximum outer diameter is 2mm greater than the mount diameter, except for the 62mm and 72mm, which are 3mm larger. Mounted UV Filters are clear in color and non-rotatable.

Technical Information



