

Mounted M30.5 x 0.5 - UV Cut-Off Filter



Mounted UV Filters

Stock **#46-576** 10 TO 12 DAYS



1



₹7,700.00

ADD TO CART

Qty 1-9

₹7,700.00

Qty 10+

₹7,482.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
25.5

Cut-On Wavelength (nm):
390.00

Filter Thread:
M30.5 x 0.50

Glass/Filter Number:

L-39
Substrate: Hoya L-39
Operating Temperature (°C): -15 to +70
Coating: Uncoated
Color: Clear
Outer Diameter (mm): 32.5
Thickness with Mount (mm): 4.50
Surface Quality: 80-50
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Type: Mounted Imaging Filter
Mount Thickness (mm): 5.2 ±0.3
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 4 - 6λ
Substrate Thickness (mm): 2.5
Mount Thickness Including Threads (mm): 7

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View