

Mounted M37 x 0.75 Threaded - Red Filter



Stock #58-642 10 TO 12 DAYS

- 1 +

₹5,394.00

ADD TO CART

Qty 1-9
₹5,394.00
Qty 10+
₹5,211.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 32.5
Filter Thread: M37 x 0.75
Color: Red
Cut-On Wavelength (nm): 600.00

Glass/Filter Number: R-60
Index of Refraction n_d: 1.53
Mount Thickness (mm): 4.5 ±0.3
Mount Thickness Including Threads (mm): 6.5
Note: AR Coating: MgF ₂
Outer Diameter (mm): 39.0
Substrate: ☐ Colored Glass
Substrate Thickness (mm): 4.0
Surface Quality: 80-50
Thickness with Mount (mm): 4.50
Type: Mounted Imaging Filter
Type of Filter: Hoya R-60 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View