

Mounted M37 x 0.75 - UV Cut-Off Filter



Mounted UV Filters

Stock #54-039 8 In Stock

-

1

+

₹4,476

ADD TO CART

Volume Pricing	
Qty 1-9	₹4,476 each
Qty 10+	₹4,048 each
Need More?	Request Quote

Product Downloads

General

Type:

Mounted Imaging Filter

Physical & Mechanical Properties

Clear Aperture CA (mm):

32.0

Outer Diameter (mm):

39.0

Thickness with Mount (mm):

4.50	
	Thickness (mm):
2.00 ±0.2	
Optical Properties	
	Cut-On Wavelength (nm):
390.00	
	Glass/Filter Number:
L-39	
	Substrate: ☐
Hoya L-39	
	Coating:
AR Coated	
	Color:
Clear	
	Surface Quality:
80-50	
	Coating Specification:
R _{avg} >2% @ 400 - 700nm	
	Wavelength Range (nm):
350 - 2200	
	Surface Flatness (P-V):
4 - 6λ	
Threading & Mounting	
	Filter Thread:
M37 x0.75	
Environmental & Durability Factors	
	Operating Temperature (°C):
-15 to +70	
Regulatory Compliance	
	Certificate of Conformance:
View	

Product Details

- Blocks UV and Transmits Visible
- Ideal as Dust or Protective Covers for Camera Sensors

Mounted UV Filters are offered with standard photographic and lens filter mount threads. These filters are ideal for applications where UV light needs to be blocked and visible light passed. The mounted clear aperture is 5mm less than the mount diameter. The maximum outer diameter is 2mm greater than the mount diameter, except for the 62mm and 72mm, which are 3mm larger. Mounted UV Filters are clear in color and non-rotatable.

Technical Information

