

[See all 17 Products in Family](#)

## Mounted M40.5 x 0.5 - UV Cut-Off Filter



Mounted UV Filters

Stock #54-725 CLEARANCE **13 In Stock**

MRP ₹4,692

Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹4,692 each                   |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

### General

Mounted Imaging Filter Type:

### Physical & Mechanical Properties

37.0 Clear Aperture CA (mm):

42.0 Outer Diameter (mm):

5.00 Thickness with Mount (mm):

2.00 ±0.2 Thickness (mm):

## Optical Properties

390.00 Cut-On Wavelength (nm):

L-39 Glass/Filter Number:

Hoya L-39 Substrate:

AR Coated Coating:

Clear Color:

80-50 Surface Quality:

$R_{avg} > 2\%$  @ 400 - 700nm Coating Specification:

350 - 2200 Wavelength Range (nm):

4 - 6λ Surface Flatness (P-V):

## Threading & Mounting

M40.5 x 0.50 Filter Thread:

## Environmental & Durability Factors

-15 to +70 Operating Temperature (°C):

## Regulatory Compliance

[View](#) Certificate of Conformance:

Japan Country of Origin:

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Blocks UV and Transmits Visible
- Ideal as Dust or Protective Covers for Camera Sensors

Mounted UV Filters are offered with standard photographic and lens filter mount threads. These filters are ideal for applications where UV light needs to be blocked and visible light passed. The mounted clear aperture is 5mm less than the mount diameter. The maximum outer diameter is 2mm greater than the mount diameter, except for the 62mm and 72mm, which are 3mm larger. Mounted UV Filters are clear in color and non-rotatable.

## Technical Information



