

Mounted M46 x 0.75 Threaded - Red Filter



Stock #54-762 10 TO 12 DAYS

- 1 +

₹4,916.00

ADD TO CART

Qty 1-9
₹4,916.00
Qty 10+
₹4,568.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
41.5

Filter Thread:
M46 x 0.75

Color:
Red

Cut-On Wavelength (nm):
600.00

Glass/Filter Number: R-60
Index of Refraction n_d: 1.53
Mount Thickness (mm): 4.4 ±0.1
Mount Thickness Including Threads (mm): 6.4
Note: AR Coating: MgF ₂
Outer Diameter (mm): 48.0
Substrate: ☐ Colored Glass
Substrate Thickness (mm): 2.5
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.5
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya R-60 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View