

[See all 17 Products in Family](#)

Mounted M58 x 0.75 - UV Cut-Off Filter



Mounted UV Filters

Stock **#54-046** **1 In Stock**

- 1 + MRP ₹7,164

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹7,164 each
Qty 10-25	₹6,457 each
Need More?	Request Quote

Product Downloads

General

Mounted Imaging Filter **Type:**

Physical & Mechanical Properties

53.0 **Clear Aperture CA (mm):**

60.0 **Outer Diameter (mm):**

Thickness with Mount (mm):
4.50

Thickness (mm):
2.00 ±0.2

Optical Properties

Cut-On Wavelength (nm):
390.00

Class/Filter Number:
L-39

Substrate:
Hoya L-39

Coating:
AR Coated

Color:
Clear

Surface Quality:
80-50

Coating Specification:
 $R_{avg} > 2\% @ 400 - 700nm$

Wavelength Range (nm):
350 - 2200

Surface Flatness (P-V):
4 - 6λ

Threading & Mounting

Filter Thread:
M58 x 0.75

Environmental & Durability Factors

Operating Temperature (°C):
-15 to +70

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
Japan

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Blocks UV and Transmits Visible
- Ideal as Dust or Protective Covers for Camera Sensors

Mounted UV Filters are offered with standard photographic and lens filter mount threads. These filters are ideal for applications where UV light needs to be blocked and visible light passed. The mounted clear aperture is 5mm less than the mount diameter. The maximum outer diameter is 2mm greater than the mount diameter, except for the 62mm and 72mm, which are 3mm larger. Mounted UV Filters are clear in color and non-rotatable.

Technical Information



