

Mounted M72 x 0.75 Threaded - Red Filter



Stock #46-535 CLEARANCE 10 TO 12 DAYS

-

1

+

₹4,867.65

ADD TO CART

Qty 1+
₹4,867.65

Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
68.0

Filter Thread:
M72 x0.75

Color:
Red

Cut-On Wavelength (nm):
600.00

Glass/Filter Number:
R-60

Index of Refraction n_d: 1.53
Mount Thickness (mm): 4.9 ±0.1
Mount Thickness Including Threads (mm): 7.4
Note: AR Coating: MgF ₂
Outer Diameter (mm): 75.0
Substrate: ☐ Colored Glass
Substrate Thickness (mm): 2.5
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.5
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya R-60 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View