

Mounted M86 x 1.0 - UV Cut-Off Filter



Mounted UV Filters

Stock **#64-895** CLEARANCE 10 TO 12 DAYS

-

1

+

₹8,910

ADD TO CART

Qty 1+

₹8,910

Volume Pricing

[Request Quote](#)

Product Downloads

SPECIFICATIONS

General

Type:
Mbunted Imaging Filter

Physical & Mechanical Properties

Clear Aperture CA (mm):

81.0	
89.0 +0/-0.2	Outer Diameter (mm):
5.00	Thickness with Mount (mm):
2.00	Thickness (mm):
±0.2	Thickness Tolerance (mm):
Optical Properties	
390.00	Cut-On Wavelength (nm):
L-39	Glass/Filter Number:
Hoya L-39	Substrate: ☐
Multi-coated	Coating:
Clear	Color:
80-50	Surface Quality:
R _{avg} >2% @ 500 - 700nm	Coating Specification:
350 - 2200	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):
Threading & Mounting	
M86 x 1.00	Filter Thread:
7.0	Mount Thickness Including Threads (mm):
Environmental & Durability Factors	
-15 to +70	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS:
View	Certificate of Conformance:

PRODUCT DETAILS

- Blocks UV and Transmits Visible
- Ideal as Dust or Protective Covers for Camera Sensors

Mounted UV Filters are offered with standard photographic and lens filter mount threads. These filters are ideal for applications where UV light needs to be blocked and visible light passed. The mounted clear aperture is 5mm less than the mount diameter. The maximum outer diameter is 2mm greater than the mount diameter, except for the 62mm and 72mm, which are 3mm larger. Mounted UV Filters are clear in color and non-rotatable.

TECHNICAL INFORMATION



