

TECHSPEC[®] Multi-Element Variable Aperture Joining Ring



Multi-Element Variable Aperture Joining Ring

Stock **#11-176** **2 In Stock**

-

1

+

₹11,076

ADD TO CART

Volume Pricing	
Qty 1-4	₹11,076 each
Qty 5-9	₹9,756 each
Qty 10+	₹8,985 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Function:

Iris Diaphragm

Physical & Mechanical Properties

6.0	Extension Length (mm):
12.0	Total Length (mm):
0.8 - 15.0	Clear Aperture CA (mm):
Matte Black Anodized Aluminum (6061-T6)	Construction:
32.0	Outer Diameter (mm):
Threading & Mounting	
M29 x0.75	Thread Type:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:

PRODUCT DETAILS

- Continuous M29 x0.75 Internal Threading for Easy Lens Spacing
- Prevent Unwanted External and Stray Light from Entering the System
- Available in Multiple Lengths for Compact Systems
- Click [Here](#) to See How to Use the Multi-Element Tube System Components to Build an Optical System.

TECHSPEC® Multi-Element Outer Tubes provide a compact and contained system mounting solution. Available in five different lengths, these outer tubes allow for control of overall system length. The enclosed design and matte finish helps prevent unwanted external and stray light from entering the optical system. TECHSPEC® Multi-Element Outer Tubes feature M29 x0.75 internal threads along the entire optical axis, allowing for infinite optical spacing adjustment for both [TECHSPEC® Multi-Element Inner Single Optic Mounts](#) and [TECHSPEC® Multi-Element Inner Pair Optic Mounts](#). For harsh environment applications, the Multi-Element Retaining Ring Set ([#37-774](#)) is highly recommended to lock in lens spacing.

Note: The [TECHSPEC® Multi-Element Tube System Accessories](#) are recommended for easy system expansion or integration. The Multi-Element 2" Square Cage Interface Plate ([#11-213](#)) can be used to mount a Multi-Element Tube System Assembly to a [TECHSPEC Stainless Steel Mounting Post](#).