

Multi-Line 150mW, 4 Lines Selectable, Argon-Ion Laser



Stock #58-453 10 TO 12 DAYS

- 1 +

₹956,565.00

ADD TO CART

Qty 1+
₹956,565.00

Volume Pricing
Request Quote

Get Product Downloads



Output Power (mW):
150

Polarization:
>100:1

Power Stability (%):
<±1

Dimensions (inches):
5.06 H x 7.60 W x 13.00 L

Spatial Mode:
TEM₀₀

Wavelength (nm): 457.00 / 488 / 514 / Multi-Line
Weight (kg): 5.9
Power Consumption (W): 1500.00
Power Supply: 100 - 265 VAC, 60/50 Hz
Warm-Up Time (minutes): 5.00
Slow Start Delay (ms): 30000.00
Pointing Accuracy (μrad): <30
Note: Output Power (mW) Total: 150 8 @457 nm, 40 @ 488 nm, 50 @ 514 nm
RMS Noise: 30 Hz - 10 MHz <1%
Beam Diameter (mm): 0.65
Output Type: Free Space
Type of Laser: Argon
Beam Divergence (mrad): 0.95
Laser Class - CDRH: IIIb
Color: Blue-Green

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View