

[See all 10 Products in Family](#)

Nikon 200mm Tube Lens

See More by [Nikon](#)



#58-520: Nikon 200mm Tube Lens

Stock **#58-520** **4 In Stock**

1 MRP ₹63,720

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹63,720 each
Need More?	Request Quote

Product Downloads

General

Tube Lens **Type:**
Nikon **Manufacturer:**

Physical & Mechanical Properties

29.00 **Length (mm):**
Maximum Diameter (mm):

Optical Properties

200.00 **Focal Length FL (mm):**

1X **Magnification:**

400 - 700 **Wavelength Range (nm):**

26.5 **Field Number (mm):**

32.0 **Entrance Pupil Diameter (mm):**

Threading & Mounting

M38 x 0.5 **Mounting Threads:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

China **Country of Origin:**


Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Superior UV Transmission
- High Numerical Aperture Designs
- Feature Low Auto-Fluorescence Materials

Nikon CFI Super Fluor Objectives are designed to provide superior transmission to ultraviolet applications operating down to 340nm, including for use with fluorochromes indo-1, fura-2, and fluo-3, or for photo-activation of caged compounds. Nikon CFI Super Fluor Objectives are designed using low auto-fluorescence materials along with high numerical apertures to guarantee sharp, bright fluorescence images. These microscope objectives have been optimized for improved signal-to-noise ratios at short wavelengths.

Technical Information



Dimensions (mm)						
Stock No.	Magnification	Parfocal Length	A	B	C	D
#75-345	4X	60.06	30.0	44.3	19.7	M25 x 0.75
#88-375	10X	60.06	32.0	58.9	12.0	M25 x 0.75
#88-376	20X	59.90	33.5	58.9	9.0	M25 x 0.75
#75-346	40X	60.06	32.0	59.8	8.3	M25 x 0.75

