

[See all 2 Products in Family](#)

Norland Index Matching Liquid (IML) 150 Preloaded Syringe, 30cc

See More by [Norland](#)



Norland Index Matching Liquid (IML) 150 Preloaded Syringe, 30cc

Stock **#17-408** **1 In Stock**

MRP ₹6,372

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹6,372 each
Qty 5-11	₹5,735 each
Need More?	Request Quote

Product Downloads

General

1 **Size (oz):**
 IML 150 **Norland Number:**
 8 months **Shelf Life:**
Type:

Barrel

Note:

Requires [30cc Hand Plunger](#) or [30cc DispensGun](#) and [Dispensing Tips](#) for use

Optical Properties

Index of Refraction (n_d):

1.52

Material Properties

Viscosity (cps):

100

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 251:

[Compliant](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- 1.52 Index of Refraction at 589nm
- Ideal for Temporary Fiber Slicing
- 6g or 30g Preloaded Syringes

Norland Index Matching Liquid (IML) 150 is a low viscosity liquid monomer used as an index matching media for temporary fiber slicing. Unlike silicone index matching liquids which are difficult to completely remove from a fiber end after use, IML 150 is easily removed using acetone. This index matching liquid can also be used between two optical elements to eliminate reflection losses caused by glass-air interfaces. Norland Index Matching Liquid (IML) 150 is available in preloaded syringes with either 6g or 30g of liquid. IML 150 does not cure and will always remain a liquid.