

[See all 2 Products in Family](#)

Norland Index Matching Liquid (IML) 150 Preloaded Syringe, 6cc

See More by [Norland](#)



Norland Index Matching Liquid (IML) 150 Preloaded Syringe, 6cc

Stock **#17-407** **5 In Stock**

MRP ₹3,186

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹3,186 each
Qty 5-11	₹2,867 each
Need More?	Request Quote

Product Downloads

General

0.20 **Size (oz):**

IML 150 **Norland Number:**

8 months **Shelf Life:**

Type:

Barrel

Optical Properties

1.52 **Index of Refraction (n_d):**

Material Properties

100 **Viscosity (cps):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 253:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 1.52 Index of Refraction at 589nm
- Ideal for Temporary Fiber Slicing
- 6g or 30g Preloaded Syringes

Norland Index Matching Liquid (IML) 150 is a low viscosity liquid monomer used as an index matching media for temporary fiber slicing. Unlike silicone index matching liquids which are difficult to completely remove from a fiber end after use, IML 150 is easily removed using acetone. This index matching liquid can also be used between two optical elements to eliminate reflection losses caused by glass-air interfaces. Norland Index Matching Liquid (IML) 150 is available in preloaded syringes with either 6g or 30g of liquid. IML 150 does not cure and will always remain a liquid.