

# NUV M43 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-689 10 TO 12 DAYS

- 1 + ₹14,790.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| ₹14,790.00                    |
| Qty 10+                       |
| ₹14,094.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

## Get Product Downloads

**Blocking Wavelength Range (nm):**  
200-250, 400-667

**Clear Aperture CA (mm):**  
38.00

**Coating:**  
Hard Coated

**Filter Thread:**

|                                                        |
|--------------------------------------------------------|
| M43 x 0.75                                             |
| <b>Color:</b><br>NUV                                   |
| <b>Center Wavelength CWL (nm):</b><br>324.00           |
| <b>Construction:</b><br>Mounted in Black Anodized Ring |
| <b>Full Width-Half Max FWHM (nm):</b><br>105.00        |
| <b>Mount Thickness (mm):</b><br>5.2                    |
| <b>Mount Thickness Including Threads (mm):</b><br>7.0  |
| <b>Outer Diameter (mm):</b><br>45.00                   |
| <b>Substrate Thickness (mm):</b><br>1.3                |
| <b>Type:</b><br>Mounted Imaging Filter                 |
| <b>Minimum Transmission (%):</b><br>≥85                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |