

[See all 12 Products in Family](#)

# Oblique Standard Contrast Cartridge for SZX2-ILLTQ/S

See More by [Olympus](#)



Oblique Standard Contrast Cartridge for SZX2-ILLTQ/S

Stock **#89-506** NEW **1 In Stock**

1  MRP ₹47,790

 Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹47,790 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Model Number:**  
N5733200

**Type of Illumination:**  
Oblique Standard

### Physical & Mechanical Properties

**Diameter (mm):**  
80.00

**Weight (g):**

## Optical Properties

35.00 **Working Distance (mm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

Japan **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- Single or Quad Position LED Turret Options Available
- Multi-Contrast Cartridge System
- Cool, Efficient LED Lighting with a 60,000-Hour Lifespan
- Slim, Ergonomic Design

Olympus LED Transmitted Light Illumination Bases are designed for use with the Olympus Stereo Microscopes [SZX](#) and [SZ](#) to enhance research with precise and flexible illumination control. Offering both quad and single LED position models, these bases support a wide range of contrast methods through an interchangeable cartridge system—brightfield (low, standard, high), oblique, darkfield, polarized, and shutter cartridges are available. The slim 41.5mm profile of this base provides a lower eyepoint and unobstructed access to samples, improving both comfort and efficiency during long observation sessions. Olympus LED Transmitted Light Illumination Bases use high-efficiency LEDs that generate minimal heat, reducing sample damage while delivering up to 60,000 hours of consistent illumination. These bases are ideal for integration into research systems where unmatched flexibility and control in stereomicroscopic imaging are required.

**Note:** Power Supply ([#89-503](#)) and Power Cable are required for use and Sold Separately. US power supply cable ([#19-529](#)); EU power supply cable ([#15-279](#))