


[See all 3 Products in Family](#)

OD 0.04 - 2.0, 50.8 x 25.4mm Stepped ND Filter



Stock **#64-383** [CONTACT US](#)

- 1 + ₹16,893

[ADD TO CART](#)

Volume Pricing	
Qty 1-10	₹16,893 each
Qty 11-25	₹15,259 each
Qty 26-49	₹14,480 each
Need More?	Request Quote

Product Downloads

General

Neutral Density Filter **Type:**

Physical & Mechanical Properties

25.4 x 50.8 **Dimensions (mm):**

2.0 **Length (inches):**

Length (mm):
50.80

Thickness (inches):
0.062

Width (inches):
1.0

Width (mm):
25.40

Optical Properties

Optical Density OD (Average):
0.04 - 2.0

Substrate:
Float Glass

Coating:
Stepped Variable

Blocking Wavelength Range (nm):
400 - 700

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
China


Imported By:
Edmund Optics India Private Limited

Product Details

- 11 Discrete Density Steps
- Design Wavelength of 400 - 700nm
- Density Neutrality of $\pm 5\%$

Density and transmission vary in eleven equal steps across the surface length. The steps are abrupt changes and no light escapes between them. Spectrally flat neutral density coating. Ideal for applications requiring variable densities and known density values.

Technical Information



Compatible Mounts