

SCHOTT OG-590, 25.4mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#46-063**

10 TO 12 DAYS

-

1

+

₹3,371.00

ADD TO CART

Qty 1-10
₹3,371.00
Qty 11+
₹3,306.00
Volume Pricing
Request Quote

Get Product Downloads
Diameter (mm): 25.40
Cut-Off Position λ_c (nm): 590±6
Cut-On Wavelength (nm):

590.00
Density (g/cm³): 2.56
Glass/Filter Number: SCHOTT OG590
Coating: Uncoated
Color: Red
Passband Limit 1 λ_{p1} (nm): 660.00
Spectral Transmittance t_p (%): 93.00
Stopband Limit λ_s (nm): 510.00
Surface Quality: 80-50
Transformation Temperature (°C): 506.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View