

Olympus LMPLFLN 10X Objective

See More by [Olympus](#)



Stock #88-203 10 TO 12 DAYS

-

1

+

₹138,330.00

ADD TO CART

Qty 1+
₹138,330.00

Volume Pricing
Request Quote

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Diameter (mm):
26.00

Field of View (mm):
2.65

Focal Length FL (mm):
18.00

Model Number:
1-U2M343

Length excluding Threads (mm): 24.00
Magnification: 10X
Maximum Diameter (mm): 26
Numerical Aperture NA: 0.25
Mounting Threads: RMS / 20.32mm x 36 TPI
Transmission (%): T> 90 from 400-700nm
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 1.34
Depth of Field (µm): 4.40
Working Distance (mm): 21.0
Weight (g): 54
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--