

# Olympus LMPLFLN-BD 20X Objective

See More by [Olympus](#)



#86-829

Stock **#86-829** 10 TO 12 DAYS

- 1 +

₹279,444.00

ADD TO CART

Qty 1+

₹279,444.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Compatible Cover Glass Thickness (mm):  
N/A

Diameter (mm):  
32.00

Field of View (mm):  
1.3

Focal Length FL (mm):  
9.00

Model Number:

|                                                                       |
|-----------------------------------------------------------------------|
| 1-U2N345                                                              |
| <b>Length excluding Threads (mm):</b><br>33.00                        |
| <b>Magnification:</b><br>20X                                          |
| <b>Maximum Diameter (mm):</b><br>32                                   |
| <b>Numerical Aperture NA:</b><br>0.40                                 |
| <b>Mounting Threads:</b><br>M26 x 36 TPI                              |
| <b>Transmission (%):</b><br>T> 90 from 400-700nm                      |
| <b>Compatible Tube Lens Focal Length (mm):</b><br>Focal Length: 180mm |
| <b>Type:</b><br>Microscope Objective                                  |
| <b>Resolving Power (µm):</b><br>0.84                                  |
| <b>Depth of Field (µm):</b><br>1.72                                   |
| <b>Working Distance (mm):</b><br>12.0                                 |
| <b>Weight (g):</b><br>86                                              |
| <b>Wavelength Range (nm):</b><br>400 - 700                            |
| <b>Style:</b><br>Infinity Corrected                                   |
| <b>Manufacturer:</b><br>Olympus                                       |
| <b>Field Number (mm):</b><br>26.5                                     |
| <b>Parfocal Length (mm):</b><br>45                                    |
| <b>Immersion Liquid:</b><br>N/A                                       |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
|------------------------------------------------------------|