

[See all 10 Products in Family](#)

Olympus SLMPLN 100X Objective

See More by [Olympus](#)



#86-826

Stock **#86-826** [CONTACT US](#)

-

1

+

₹6,66,900

ADD TO CART

Volume Pricing	
Qty 1+	₹6,66,900 each
Need More?	Request Quote

Product Downloads

General	
1-U2M275	Model Number:
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm	
Microscope Objective	Type:
Infinity Corrected	Style:
	Manufacturer:


Olympus	
Physical & Mechanical Properties	
0.26	Field of View (mm):
37.40	Length excluding Threads (mm):
26	Maximum Diameter (mm):
100	Weight (g):
Optical Properties	
N/A	Compatible Cover Glass Thickness (mm):
1.80	Focal Length FL (mm):
100X	Magnification:
0.60	Numerical Aperture NA:
T> 90 from 400-700nm	Transmission (%):
0.56	Resolving Power (μm):
0.76	Depth of Field (μm):
7.6	Working Distance (mm):
400 - 700	Wavelength Range (nm):
26.5	Field Number (mm):
45	Parfocal Length (mm):
N/A	Immersion Liquid:
Threading & Mounting	
RMS / 20.32mm x 36 TPI	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:


Product Details

- Ideal for Brightfield Microscopy
- Ultra-Long Working Distances Reduce Risk of Specimen Damage
- Over 90% Transmission from 400 – 700nm
- Additional [Olympus Infinity Corrected Objectives](#) Available


Olympus Super Long WD MPlan Achromat Infinity Corrected Objectives are ideal for electronic assembly, semiconductor inspection, or other flat field inspection applications where resolution is critical. Olympus Super Long WD M Plan Achromat Infinity Corrected Objectives provide excellent performance, ultra-long working distances, and superior image clarity.

Technical Information





Using Olympus Objectives
with C-Mount Cameras



Stock #ABCDEFG

SLMPLN 20X	86-824	20.0	0.5	0.2	16.1	25.0	26.0	4.9
SLMPLN 50X	86-825	27.0	2.2	0.7	16.9	21.4	26.0	4.9
SLMPLN 100X	86-826	37.4	1.0	0.2	14.7	23.8	26.0	4.9

