

[See all 20 Products in Family](#)

Olympus SZX7 Stereo Microscope Body

See More by [Olympus](#)



SZX7 Zoom Stereo Microscope - accessories shown not included

Stock **#88-103** **2 In Stock**

-

1

+

₹1,81,350

ADD TO CART

Volume Pricing	
Qty 1+	₹1,81,350 each
Need More?	Request Quote

Product Downloads

General	
SZX-ZB7	Model Number:
Olympus	Manufacturer:

Regulatory Compliance	
View	Certificate of Conformance:
Country of Origin:	

Product Details

- 7:1 Zoom Ratio with Video Adaptability
 - Long Working Distances
 - Accessories Expand Magnification from 4X– 336X
 - [Olympus SZ51 and SZ61 Zoom Stereo Microscopes](#) Also Available
- The Olympus SZX7 Zoom Stereo Microscope utilizes a Galilean optical system to provide superior image accuracy at high resolutions. The Olympus SZX7 Zoom Stereo Microscope offers video compatibility for image documentation and boom stand adaptability for precise positioning needs. Additionally, the SZX7 features an integrated click-stop mechanism to recall specific magnification settings. A variety of objective lenses and eyepieces are also available to provide superior image flatness to a wide range of specimens or applications, and to allow for imaging difficult-to-access samples.

Technical Information

Description	Stock No.
Microscope Body (Required)	
SZX7 Stereo Microscope Body	#88-103
Stands (One Required)	
Basic Reflected Light Stand with Reversible Stage Plate	#88-207
Transmitted and Reflected LED Light Stand	#88-208
Observation Tubes (One Required)	
30° Binocular Observation Tube	#88-106
30° Trinocular Observation Tube (Camera Adapter Required)	#88-107
Eyepieces (Two Required)	
10XWidefield Eyepiece	#88-108
15XWidefield Eyepiece	#88-109
20XWidefield Eyepiece	#88-110
30XWidefield Eyepiece	#88-111
Objectives (One Required)	
0.5XAchromatic Objective Lens	#33-254
1XAchromatic Objective Lens	#88-112
1.25XAchromatic Objective Lens	#88-113
0.75XPlan Achromatic Objective Lens	#88-114
2XPlan Achromatic Objective Lens	#88-115
1XPlan Apochromatic Objective Lens	#88-116
Camera Adapters (One Required for Video/Image Capture)	
1XCamera Adapter w/ C-mount Coupler	#88-209
0.63XC-Mbunt Adapter	#11-122
0.5X C-Mount Adapter	#11-123
Optional Accessories	
Ball & Socket Stage for Basic Light Stand	#88-123

Objective Lens	10XEyepiece #88-108		15XEyepiece #88-109		20XEyepiece #88-110		30XEyepiece #88-111	
	F.N. 22		F.N. 16		F.N. 12.5		F.N. 7	
	Mag.	FOV (mm)	Mag.	FOV (mm)	Mag.	FOV (mm)	Mag.	FOV (mm)
0.5X	4X-28X	55 - 7.8	6X-42X	40 - 5.7	8X-56X	31.3 - 4.5	12X-84X	17.5 - 2.5
0.75X	6X-42X	36.7 - 5.2	9X-63X	26.7 - 3.8	12X-84X	20.8 - 3	18X-126X	11.7 - 1.7
1X	8X-56X	27.5 - 3.9	12X-84X	20 - 2.9	16X-112X	15.6 - 2.2	24X-168X	8.8 - 1.3
1.25X	10X-70X	22 - 3.1	15X-105X	16 - 2.3	20X-140X	12.5 - 1.8	30X-210X	7.0 - 1.0
1.5X	12X-84X	18.3 - 2.6	18X-126X	13.3 - 1.9	24X-168X	10.4 - 1.5	36X-252X	5.8 - 0.83
2X	16X-112X	13.8 - 1.9	24X-168X	10 - 1.4	32X-224X	7.8 - 1.1	48X-336X	4.4 - 0.63

Olympus SZ51/SZ62					Olympus SZX7			
Affordably priced with high resolving power					Larger zoom ratio than the SZ51/SZ61			
Utilizes a Greenough optical system					Brighter, higher resolution images			
					Utilizes an advanced Galilean optical system			

