

TECHSPEC®

One Knob Stage & 12" Track Combination



One Knob Stage and Track Combination

Stock **#59-337** 10 TO 12 DAYS



1



₹24,882.00

ADD TO CART

Qty 1+

₹24,882.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Type of Drive:
Rack and Pinion

Type:
English

Stage Size (mm):
62 x 60

Travel (inches):
12

Construction: Black Anodized Aluminum
Graduation (inches): Track: 0.1 Vernier Reading: 0.01
Load Capacity, Normal (kg): 5
Load Capacity, Vertical (kg): 2
Mounting Threads: (9) ¼-20 on Carrier
Note: Track & One Knob Carrier Set
S.H.C.S. C'bore: (6) 0.27" Thru on Track
Straight Line Accuracy (mm): 0.1 - 0.25
Travel Per Knob Rotation (inches): 0.71

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View