

## Orange M37 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-558 10 TO 12 DAYS



1



₹13,485.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| ₹13,485.00                    |
| Qty 10+                       |
| ₹12,815.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

**Blocking Wavelength Range (nm):**  
200-530, 650-1049

**Clear Aperture CA (mm):**  
32.50

**Coating:**  
Hard Coated

**Filter Thread:**

|                                                        |
|--------------------------------------------------------|
| M37 x 0.75                                             |
| <b>Color:</b><br>Orange                                |
| <b>Center Wavelength CWL (nm):</b><br>590.00           |
| <b>Construction:</b><br>Mounted in Black Anodized Ring |
| <b>Full Width-Half Max FWHM (nm):</b><br>75.00         |
| <b>Mount Thickness (mm):</b><br>5.2                    |
| <b>Mount Thickness Including Threads (mm):</b><br>7.0  |
| <b>Outer Diameter (mm):</b><br>39.00                   |
| <b>Substrate Thickness (mm):</b><br>1.3                |
| <b>Type:</b><br>Mounted Imaging Filter                 |
| <b>Minimum Transmission (%):</b><br>≥85                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |