

Orange M37.5 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-677 10 TO 12 DAYS

⊖ 1 ⊕

₹13,485.00

ADD TO CART

Qty 1-9
₹13,485.00
Qty 10+
₹12,815.00
Volume Pricing
Request Quote

Get Product Downloads

Blocking Wavelength Range (nm):
200-530, 650-1056

Clear Aperture CA (mm):
32.50

Coating:
Hard Coated

Filter Thread:

M37.5 x 0.50
Color: Orange
Center Wavelength CWL (nm): 590.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 75.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 39.50
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View