

## Pixelink M-Series M4M-CYL Microscopy Monochrome Camera



Stock #17-820 [CONTACT US](#)

MRP ₹2,52,225

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹2,52,225 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

Monochrome **Spectrum:**

### General

Monochrome Microscopy Camera **Type:**

M4M-CYL **Model Number:**

Pixelink **Manufacturer:**

M-Series **Camera Series:**

## Physical & Mechanical Properties

**Dimensions (mm):**  
85.68 x 54.01 (excludes lens mount)

**Weight (g):**  
218.5

**Housing:**  
Full

## Sensor

**Image Buffer:**  
Not Specified

**Sensor Format:**  
1"

**Resolution (Megapixels):**  
4.20

**Frame Rate (fps):**  
90.30

**Pixels (H x V):**  
2,048 x 2,048

**Pixel Size, H x V (µm):**  
5.5 x 5.5

**Sensing Area, H x V (mm):**  
11.3 x 11.3

**Imaging Sensor:**  
CMOSIS CM4000

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Global

**Pixel Depth:**  
8/10 bit

**Exposure Time:**  
Not Specified

**Dynamic Range (dB):**  
60

**Machine Vision Standard:**  
USB3 Vision

## Electrical

**Power Consumption (W):**  
Not Specified

## Hardware & Interface Connectivity

**Interface:**  
USB 3.0

**Connector:**  
USB 3.0, Micro-B

**Power Supply:**  
Power over USB

**GPIOs:**  
None

**Synchronization:**  
Software Trigger

**Interface Port Orientation:**  
Back Panel

**GPIO Connector Type:**  
None

## Threading & Mounting

**Mount:**  
C-Mount

**Mounting Threads:**  
No Mounting Threads/Tripod Adapter

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +50

**Storage Temperature (°C):**  
-45 to +85

## Regulatory Compliance

**RoHS 2015:**  
Compliant

Compliant

Reach 224:

[View](#)

Certificate of Conformance:

Canada

Country of Origin:

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- High Resolution Sensors up to 20 MegaPixel
- Pixelink® Capture Software Included
- Compact Form Factor
- Optional Three-Tier  $\mu$ Scope Microscopy Software

Pixelink® M-Series Microscopy Cameras provide cost-effective, high-resolution imaging capabilities for both brightfield and darkfield microscopy. These cameras are designed to capture high resolution images at up to 20MP and are available with various sensor sizes and frame rates. These cameras include a USB 3.0 cable and Pixelink® Capture Software, making it easy to integrate into existing microscopy systems in a variety of laboratory settings. The optional three-tier  $\mu$ Scope Microscopy Software (Essentials, Standard, Professional) offers advanced microscopy targeted features and measurement tools such as live measurement, time lapse capture, and live image comparison. Pixelink® M-Series Microscopy Cameras are ideal for demanding applications requiring high resolution and low noise imaging including life science, metrology, and medical imaging.

**Note:** Pixelink® Capture Software available for download. USB 3.0 cable included.