

[See all 16 Products in Family](#)

Pixelink PL-X9524MG-T 1.1" 20MP TFL Mount, 10GigE PoE Monochrome Camera



Pixelink® PL-X 10GigE Cameras



Stock #23-889 **1 In Stock**

- 1 + MRP ₹5,85,162

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹5,85,162 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Camera **Type:**

Model Number:

PL-X9524MG-T

Pixelink **Manufacturer:**

PL-XSeries **Camera Series:**

Physical & Mechanical Properties

125 x 57 x 57 **Dimensions (mm):**

560.0 **Weight (g):**

Full **Housing:**

Sensor

Not Specified **Image Buffer:**

1.2" **Sensor Format:**

24.00 **Resolution (Megapixels):**

43.00 **Frame Rate (fps):**

5,328 x 4,608 **Pixels (H x V):**

2.74 x 2.74 **Pixel Size, H x V (µm):**

14.6 x 12.6 **Sensing Area, H x V (mm):**

Sony IMX530 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

8/12 bit **Pixel Depth:**

Not Specified **Exposure Time:**

70 **Dynamic Range (dB):**

10GigE Vision **Machine Vision Standard:**

Electrical

5V (from USB Type-C connector), 48V (802.3bt PoE) **Power Consumption (W):**

Hardware & Interface Connectivity

GigE (PoE) **Interface:**

GiGE, USB 3.0, Micro-C **Connector:**

PoE or USB **Power Supply:**

1 opto-isolated input, 2 non-isolated GPIOs **GPIOs:**

Hardware and Software Trigger **Synchronization:**

Back Panel **Interface Port Orientation:**

M12 X-Coded (8-pin) **GPIO Connector Type:**

Threading & Mounting

TFL-Mount **Mount:**

No Mounting Threads/Tripod Adapter **Mounting Threads:**

Environmental & Durability Factors

0°C to 50°C **Operating Temperature (°C):**

Storage Temperature (°C):

-45°C to 85°C

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

Canada **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 10GBASE-T (10GigE) Ethernet Interface, 10X Faster than GigE
- 7.0 to 24.0 Megapixel Sony 4th Gen Pregius S Sensors
- Fully Compatible with Pixelink Capture Software and SDK

Pixelink PL-X 10GigE Cameras, utilizing the latest 10GBASE-T Gigabit Ethernet interface, are capable of providing high quality, reliable image transfers at cable lengths of up to 100m on CAT6A. These global shutter cameras offer up to 24MP Resolution with framerates up to 154FPS via the Sony Pregius 2nd, 3rd and 4th generation sensors. Additionally, these cameras feature Power over Ethernet (PoE), Trigger over Ethernet (ToE) and IEEE1588 clock synchronization (PTP), and are fully compatible with Pixelink Capture Software and SDK. Pixelink PL-X10GigE Cameras are ideal for three-dimensional mapping, analytical research, AR/VR applications, as well as automated inspection and life science imaging.

Note: Pixelink Capture is a free, user-friendly application included with all Pixelink cameras, offering real-time image and video capture through an intuitive graphical interface. In contrast, the Pixelink SDK is a comprehensive development toolkit for Windows and Linux that enables developers to build custom applications with full camera control via C/C++, .NET, or Python. The SDK is available as a trial download, allowing users to evaluate its capabilities before purchasing a license. Links to software downloads (SDK and Capture) are available on the product pages.