

[See all 13 Products in Family](#)

PL-D753CU-S-AFE-BL PixeLINK USB 3.0 Autofocus Color Camera



Pixelink® USB 3.0 Autofocus Liquid Lens Board Level Cameras

Stock #14-176 [CONTACT US](#)

1 [-](#) [+](#) MRP ₹1,94,877

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,94,877 each
Need More?	Request Quote

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

PL-D753CU-S-AFE-BL **Model Number:**

Pixelink **Manufacturer:**

Camera Series:

Physical & Mechanical Properties

Dimensions (mm):
50.8 x 35 x 13.36 (excludes lens mount)

Weight (g):
35.8

Housing:
Board Level

Sensor

Image Buffer:
Not Specified

Sensor Format:
2/3"

Resolution (Megapixels):
2.80

Frame Rate (fps):
141.00

Pixels (H x V):
1,936 x 1,464

Pixel Size, H x V (µm):
4.5 x 4.5

Sensing Area, H x V (mm):
8.71 x 6.59

Imaging Sensor:
Sony IMX421

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Global

Pixel Depth:
8/12 bit

Exposure Time:
10µs - 120s

Dynamic Range (dB):
72

Machine Vision Standard:
USB3 Vision v1.0

Electrical

Power Consumption (W):
Not Specified

Hardware & Interface Connectivity

Interface:
USB 3.0

Connector:
USB 3.0, Micro-B

Power Supply:
Power over USB

GPIOs:
1 opto-isolated trigger input, 2 non-isolated outputs,
1 non-isolated input

Synchronization:
Hardware Trigger (GPIO) or Software Trigger

Interface Port Orientation:
Side Panel

GPIO Connector Type:
8-pin Molex 1.25mm Pitch

Operating System:
Software Driver: Windows 32 and 64 bit

Threading & Mounting

Mount:
S-Mount (M12 x 0.5)

Mounting Threads:
No Mounting Threads/Tripod Adapter

Environmental & Durability Factors

Operating Temperature (°C):
0 to +50

Storage Temperature (°C):
-45 to +85

Regulatory Compliance

Compliant

RoHS 2015:

Compliant

Reach 224:

[View](#)

Certificate of Conformance:

Canada

Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- M12 S-Mount Board Level Cameras
- Seamless Integration of Liquid Lenses
- One-Push Autofocus, High Speed Focus Movement

Pixelink® USB 3.0 Autofocus Liquid Lens Board Level Cameras provide one push, high-speed, point to point focus by utilizing liquid lens integration. These USB 3.0 board level cameras feature a M12 S-Mount camera mount. With seamless liquid lens control via the included software and easy integration with the Pixelink SDK, these cameras are ideal for high-speed imaging applications such as bar-code reading and biometrics.

Note: Board level cameras with exposed electronics are intended for system integration and may not be suitable for end users. Liquid lens is not included.

To get started, please choose your camera and the appropriate TECHSPEC® Liquid Lens M12 Lenses listed under the Accessories section. These lenses are available in 6mm, 8mm, 12mm, and 16mm focal lengths.

Pixelink Capture is a free, user-friendly application included with all Pixelink cameras, offering real-time image and video capture through an intuitive graphical interface. In contrast, the Pixelink SDK is a comprehensive development toolkit for Windows and Linux that enables developers to build custom applications with full camera control via C/C++, .NET, or Python. The SDK is available as a trial download, allowing users to evaluate its capabilities before purchasing a license. Links to software downloads (SDK and Capture) are available on the product pages.