

[See all 62 Products in Family](#)

## Pixelink PL-D755CU-T, 2/3" 5.0MP, C-Mount USB 3.0 Color Camera



Pixelink® USB 3.0 Cameras (Full Housing)



Stock #11-437 **1 In Stock**

[Similar Cameras](#)

1 MRP ₹2,20,070

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹2,20,070 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

Color Spectrum:

### General

Color Camera Type:

PL-D755CU-T Model Number:

Pixelink  
Manufacturer:  
PL-D  
Camera Series:

## Physical & Mechanical Properties

Dimensions (mm):  
55 x 38.5 x 27 (excludes connectors and lens mount)  
Weight (g):  
89

Housing:  
Full

## Sensor

Image Buffer:  
Not Specified

Sensor Format:  
2/3"

Resolution (Megapixels):  
5.01

Frame Rate (fps):  
80.90

Pixels (H x V):  
2,448 x 2,048

Pixel Size, H x V (µm):  
3.45 x 3.45

Sensing Area, H x V (mm):  
8.45 x 7.07

Imaging Sensor:  
Sony IMX250

Type of Sensor:  
Progressive Scan CMOS

Shutter Type:  
Global

Pixel Depth:  
8/12 bit

Exposure Time:  
20µs - 120s

Dynamic Range (dB):  
70

Machine Vision Standard:  
USB3 Vision v1.0

## Electrical

Power Consumption (W):  
Not Specified

## Hardware & Interface Connectivity

Interface:  
USB 3.0

Connector:  
USB 3.0, Micro-B

Power Supply:  
Power over USB

GPIOs:  
1 opto-isolated trigger input, 1 opto-isolated output, 2 non-isolated outputs, 1 non-isolated input

Synchronization:  
Hardware Trigger (GPIO) or Software Trigger

Interface Port Orientation:  
Side Panel

GPIO Connector Type:  
8-pin Hirose (HR25)

Operating System:  
Software Driver: Windows 32 and 64 bit

## Threading & Mounting

Mount:  
C-Mount

Mounting Threads:  
1/4-20 with Tripod Mount Adapter [#89-408](#)

## Environmental & Durability Factors

Operating Temperature (°C):  
0 to +50

-45 to +85 **Storage Temperature (°C):**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**Compliant** **Reach 224:**

**View** **Certificate of Conformance:**

Canada **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Resolutions Up to 20MP
- Sensor Sizes from 1/2.5" to 1.1"
- Right Angle Housing and Board Level Configurations Available

Pixelink® USB 3.0 Cameras are high resolution and high-speed solutions to applications ranging from biometrics to surveillance. Pixelink® USB 3.0 Cameras feature resolutions of up to 20MP, frame rates of up to 170fps, and USB 3.0 compatibility for power and high data throughput. The right angle housing configurations also feature a GPIO to enable triggering to ease system integration. Pixelink® USB 3.0 Cameras also compatible with sensor sizes ranging from 1/2.5" to 1.1" and are ideal for inspecting weld and PCB and flat panel displays. These cameras are available in monochrome or color.

**Note:** Mounting Adapters are only designed for enclosed camera models, and not board-level. If your camera ends in "-BL", it does not have a compatible mount.

Pixelink Capture is a free, user-friendly application included with all Pixelink cameras, offering real-time image and video capture through an intuitive graphical interface. In contrast, the Pixelink SDK is a comprehensive development toolkit for Windows and Linux that enables developers to build custom applications with full camera control via C/C++, .NET, or Python. The SDK is available as a trial download, allowing users to evaluate its capabilities before purchasing a license. Links to software downloads (SDK and Capture) are available on the product pages.

;