

[See all 13 Products in Family](#)

## PL-D7620CU-S-BL-AFE PixeLINK USB 3.0 Autofocus Color Board Level Camera



Pixelink® USB 3.0 Autofocus Liquid Lens Board Level Cameras

Stock #21-080 [CONTACT US](#)

1 MRP ₹1,60,362

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹1,60,362 each
Need More?	<a href="#">Request Quote</a>

Note: This item requires accessories for use | [Learn More](#)

### Product Downloads

Color Spectrum:

### General

Color Camera Type:

PL-D7620CU-S-BL-AFE Model Number:

Pixelink Manufacturer:

PL-D **Camera Series:**

## Physical & Mechanical Properties

**Dimensions (mm):**  
50.8 x 35 x 13.36 (excludes lens mount)

**Weight (g):**  
35.8

**Housing:**  
Board Level

## Sensor

**Image Buffer:**  
Not Specified

**Sensor Format:**  
1"

**Resolution (Megapixels):**  
20.00

**Frame Rate (fps):**  
20.00

**Pixels (H x V):**  
5,472 x 3,648

**Pixel Size, H x V (µm):**  
2.4 x 2.4

**Sensing Area, H x V (mm):**  
13.13 x 8.75

**Imaging Sensor:**  
Sony IMX183

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Rolling

**Pixel Depth:**  
12 bit

**Exposure Time:**  
Not Specified

**Dynamic Range (dB):**  
73.6

**Machine Vision Standard:**  
USB3 Vision v1.0

## Electrical

**Power Consumption (W):**  
Not Specified

## Hardware & Interface Connectivity

**Interface:**  
USB 3.0

**Connector:**  
USB 3.0, Micro-B

**Power Supply:**  
Power over USB

**GPIOs:**  
1 non-isolated trigger or general-purpose input, 2 non-isolated outputs

**Synchronization:**  
Hardware Trigger (GPIO) or Software Trigger

**Interface Port Orientation:**  
Side Panel

**GPIO Connector Type:**  
8-pin Mflex 1.25mm Pitch

## Threading & Mounting

**Mount:**  
S-Mount (M12 x 0.5)

**Mounting Threads:**  
No Mounting Threads/Tripod Adapter

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +50

**Storage Temperature (°C):**  
-45 to +85

## Regulatory Compliance

---

**Compliant** **RoHS 2015:**

**Compliant** **Reach 224:**

---

**View** **Certificate of Conformance:**

---

**Country of Origin:**  
Canada

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

---

## Product Details

- M12 S-Mount Board Level Cameras
- Seamless Integration of Liquid Lenses
- One-Push Autofocus, High Speed Focus Movement

Pixelink® USB 3.0 Autofocus Liquid Lens Board Level Cameras provide one push, high-speed, point to point focus by utilizing liquid lens integration. These USB 3.0 board level cameras feature a M12 S-Mount camera mount. With seamless liquid lens control via the included software and easy integration with the Pixelink SDK, these cameras are ideal for high-speed imaging applications such as bar-code reading and biometrics.

**Note:** Board level cameras with exposed electronics are intended for system integration and may not be suitable for end users. Liquid lens is not included.

To get started, please choose your camera and the appropriate TECHSPEC® Liquid Lens M12 Lenses listed under the Accessories section. These lenses are available in 6mm, 8mm, 12mm, and 16mm focal lengths.

Pixelink Capture is a free, user-friendly application included with all Pixelink cameras, offering real-time image and video capture through an intuitive graphical interface. In contrast, the Pixelink SDK is a comprehensive development toolkit for Windows and Linux that enables developers to build custom applications with full camera control via C/C++, .NET, or Python. The SDK is available as a trial download, allowing users to evaluate its capabilities before purchasing a license. Links to software downloads (SDK and Capture) are available on the product pages.

---

;