

Polarizer Mount C-Thread Adapter



#87-207: Polarizer Mount C-Thread Adapter

Stock **#87-207** **20+ In Stock**

- 1 + ₹9,095

ADD TO CART

Volume Pricing	
Qty 1-4	₹9,095 each
Qty 5-25	₹8,186 each
Qty 26-49	₹7,731 each
Need More?	Request Quote

Product Downloads

Threading & Mounting

Female C-Mount **Mounting Threads:**

34.0 **Mounting Tube Outer Diameter (mm):**

Regulatory Compliance

RoHS 2015:

Product Details

- Coarse and Fine Movement Available
- Black Anodized Aluminum
- **Posts** and **Post Holders** Required for Mounting

Metric Polarizer Mounts feature secure optic retainer, lever arm for smooth rotation, locking knob for repeatability and 360° scaled vernier. **Posts** and **Post Holders** are required for mounting to a breadboard. Micrometer version provides fine adjustment. Metric Polarizer Mounts, for Micrometer Driven version only: total travel of the 0.25mm pitch fine adjustment screw is 10°. Total angular rotation per rotation of knob is 20 minutes. *40mm total including 34mm diameter mounting tube.

Technical Information

Diameter of Compatible Optics D	Clear Aperture CA	Drive Type	Mount Diameter A	Mount Thickness B	C	E	Stock No.
Standard							
20.0	17	Standard	50	19	34	24.0	#55-454
25.4	22	Micrometer	69	-	-	33.5	#55-011
25.4	22	Standard	60	20	42	29.5	#55-010
30.0	27	Micrometer	69	-	-	33.5	#57-570
30.0	27	Standard	60	20	42	29.5	#57-569
50.0	47	Micrometer	89	-	-	43.5	#56-329
50.0	47	Standard	80	20	62	39.5	#55-455
Glan-Thompson Polarizer Mounts							
25.4	18	Micrometer	69	-*	-	33.5	#57-572
25.4	18	Standard	60	20*	42	29.5	#57-571

