

[See all 64 Products in Family](#)

Power Supply + 8-pin GPIO Y-cable, IP65/67, 5m/1.8m

See More by [IDS Imaging Development Systems](#)



#19-692: Power Supply + 8-pin GPIO Y-cable, IP65/67, 5m/1.8m

Stock **#19-692** CLEARANCE **4 In Stock**

-

1

+

 ₹21,358

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹21,358 each
Need More?	Request Quote

Product Downloads

General

Camera Accessory

Type:

Note:

8-pin Binder Connector to open end, 2 branches: one branch 6 wires for Trigger and Flash (5m), one branch to Power Supply adapter (1.8m)

Hardware & Interface Connectivity

5, 1.8

Length of Cable (m):

8-pin Binder Connector		Connector:
Regulatory Compliance		
View	Certificate of Conformance:	
Compliant	REACH 241:	
Germany		Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000		Imported By:

Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.