

[See all 78 Products in Family](#)

## Preloaded Norland Optical Adhesive NBA 108H Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#17-384** **2 In Stock**

1  MRP ₹4,195

**1** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹4,195 each
Qty 5-11	₹3,781 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

0.34 **Size (oz):**  
108H **Norland Number:**  
4 months **Shelf Life:**  
**Type:**

Barrel

**Typical Applications:**

Temporary bonding of lenses to metal polishing mounts

**Note:**

Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.

## Optical Properties

**Index of Refraction ( $n_d$ ):**

1.51

**Absorption Range (nm):**

350 - 380

## Material Properties

**Glass Bonding:**

Excellent

**Metal Bonding:**

Excellent

**Plastic Bonding:**

Fair

**Viscosity (cps):**

550

**Bonding Type:**

Glass to Metal

**Energy for Full Cure ( $J/cm^2$ ):**

6

## Environmental & Durability Factors

**Durability:**

Hard & Resilient

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 251:**

[Compliant](#)

**Country of Origin:**

United States

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

## Technical Information

**NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES**

Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.