

TECHSPEC[®] Protected Silver Coated, C-Mounted First Surface Mirror



Stock #36-154 4 In Stock

-

1

+

₹22,372

ADD TO CART

Volume Pricing	
Qty 1-4	₹22,372 each
Qty 5-9	₹19,797 each
Qty 10-25	₹18,235 each
Need More?	Request Quote

Product Downloads

General

Type of Optics:

First Surface Mirror

Type:

Flat Mirror

Mirror Included:

#89-489

Physical & Mechanical Properties

38 x38 x50	Dimensions (mm):
±0.25	Dimensional Tolerance (mm):
Ground	Edges:
38.0	Extension Length (mm):

Optical Properties	
Metal	Coating Type:
Protected Silver (450-10000nm)	Coating:
4 - 6λ	Surface Flatness (P-V):
450 - 10000	Wavelength Range (nm):
Float Glass	Substrate: □
Ravg >98% @450 - 2000nm Ravg >98% @2000 - 10,000nm	Coating Specification:
60-40	Surface Quality:

Threading & Mounting	
C-Mount (1" x32 TPI)	Thread Type:


Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Ideal for Precision Alignment
- 35 x35mm Mirror Dimensions
- 50mm H x38mm Wx38mm D Housing Dimensions
- [Mirror](#) and [Housing](#) Available Separately

TECHSPEC® C-Mounted First Surface Mirrors combine our TECHSPEC® 35mm square by 3mm thick enhanced aluminum coated first surface mirror with a C-Mount compatible housing. This mirror can be easily integrated into any optical system via four C-Mount threaded holes. The housing is 50mm H x38mm Wx38mm D, with four 1-32 TPI female threaded apertures. TECHSPEC® C-Mounted First Surface Mirrors feature a threaded aperture lid which is included to close the unused port. The base has a centered ¼-20 tapped hole for mounting to a post.

Technical Information



Coating Curves