

Hoya R60 (600nm), 50.8mm Sq., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock **#66-065** 10 TO 12 DAYS

- 1 + **₹7,656.00**

ADD TO CART

Qty 1-10

₹7,656.00

Qty 11+

₹6,786.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):
50.8 x 50.8

Cut-Off Position λ_c (nm):
600±6

Cut-On Wavelength (nm):
600.00 ±6

Density (g/cm³): 2.69
Glass/Filter Number: Hoya R60
Substrate: ☐ Colored Glass
Length (mm): 50.80
Coating: Uncoated
Color: Red
Surface Quality: 80-50
Transformation Temperature (°C): 560
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Longpass Filter
Wavelength: VIS
Width (mm): 50.80
Dimensional Tolerance (mm): ±0.38
Reflection Factor P _d : 0.92
Bevel: Protective as needed
Δλ (nm): <25
TH (%): >85

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View