

RGB Adjustable LED Ring Light



Stock #34-864 10 TO 12 DAYS

- 1 + **₹73,080.00**

ADD TO CART

Qty 1+
₹73,080.00

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color: RGB
Connector: M12, 5 pins
Inner Diameter (mm): 58.0
Input Voltage (V): 24VDC

Mount: M4 (x4) and 3.5mm Thru (x4)
Operating Temperature (°C): -10 to 50
Dimensions (mm): 151.0 x 117.0 x 40.0
Weight (g): 400
Power Supply: Power Supply Required and Sold Separately. USA: #15-874 Europe: #15-875 Japan: #15-874 Korea: #15-874 China: #15-874
Type of Illumination: LED Illuminator
Note: Power Supply #34-871 (110V) or #34-872 (220V) (sold separately) will not provide individual color control.
Geometry: Ring Light
Illumination Mode: Strobed or Constant
Environmental Rating: IP65

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View