

TECHSPEC[®] 25mm ID Rotary Mount, 1/4-20



Rotary Mount, 1/4-20, #87-529

Stock #87-529 10 TO 12 DAYS

-

1

+

₹10,353.00

ADD TO CART

Qty 1+
₹10,353.00
Volume Pricing
Request Quote

Get Product Downloads

Function: Rotary
Type of Optics: Circular/Cylindrical Tube
Plate Inner Diameter (mm): 25.0
Dimensions (mm): 50 Dia.
Bolt Circle Diameter for 6mm Dia. Thru (mm): 38.0

Bolt Circle Diameter for M3 Tapped (mm): 38.0
Thickness (mm): 21.0
Compatible Post: 1/4-20
Construction: Black Anodized Aluminum

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View