


## RS-232 Breakout Cable



RS-232 Breakout Cable (#66-035)

Stock **#66-035** [CONTACT US](#)

- 1 + MRP ₹2,655

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹2,655 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Accessory **Type of Illumination:**

### Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Reach 224:**  
[Compliant](#)

## Country of Origin:

United States

## Imported By:

Edmund Optics India Private Limited  
 267, Greystone Building, Second Floor,  
 6th Cross Rd, Binnamangala,  
 Stage 1, Indiranagar, Bengaluru,  
 Karnataka, India 560038  
 Phone: +91-80-6845 0000

## Product Details

- Direct Replacement for 150W Halogen Illuminators
- 50% Power Savings Compared To Halogen Source
- More than 60,000 Hour LED Lifetime
- For Use with [Fiber Optic Light Guides](#)

SugarCUBE™ LED Illuminators have an output of up to 1700 lumens and are ideal replacements for standard halogen illuminators because LED illuminators last up to 60 times longer than halogen bulbs and never need to be replaced. These illuminators are controllable manually through controls on the front of the unit or via RS-232 for easy integration into computer controlled systems. Optional, easy-to-operate software is also available.

Available with red, green, blue, white, or white options, SugarCUBE™ LED Illuminators fulfill a wide range of machine vision applications. The standard white unit offers an output power of greater than 1450 lumens and a radiant flux of 1200mW. A fiber optic adapter required to connect a light guide to the illuminator.

## Technical Information

Stock Number	Description	Shoulder Diameter (Inches)	Ferrule Diameter (Inches)	Compatible Illuminator	Compatible Light Guide
<a href="#">#66-301</a>	SugarCUBE™ Light Guide Adapter - 50	0.752	0.564	Red, Green, Blue, White, Ultra White	<a href="#">54-210</a> , <a href="#">39-826</a> , <a href="#">58-839</a> , <a href="#">54-174</a> , <a href="#">38-659</a> , <a href="#">39-369</a> , <a href="#">39-370</a> , <a href="#">39-371</a>  Ultra White MUST use liquid light guides
<a href="#">#66-302</a>	SugarCUBE™ Light Guide Adapter - 52	0.877	0.564	Red, Green, Blue, White, Ultra White	<a href="#">54-210</a> , <a href="#">39-826</a> , <a href="#">58-839</a> , <a href="#">54-174</a> , <a href="#">38-659</a> , <a href="#">39-369</a> , <a href="#">39-370</a> , <a href="#">39-371</a>  Ultra White MUST use liquid light guides
<a href="#">#66-303</a>	SugarCUBE™ Light Guide Adapter - 53	1.505	0.439	Red, Green, Blue, White	
<a href="#">#66-304</a>	SugarCUBE™ Light Guide Adapter - 56	0.207	0.19	Red, Green, Blue, White	<a href="#">54-199</a> , <a href="#">42-344</a> , <a href="#">39-365</a> , <a href="#">42-345</a> , <a href="#">40-644</a> , <a href="#">39-366</a>
<a href="#">#66-305</a>	SugarCUBE™ Light Guide Adapter - 57	0.255	0.19	Red, Green, Blue, White	<a href="#">54-199</a> , <a href="#">42-344</a> , <a href="#">39-365</a> , <a href="#">42-345</a> , <a href="#">40-644</a> , <a href="#">39-366</a>
<a href="#">#66-306</a>	SugarCUBE™ Light Guide Adapter - 58	0.424	0.314	Red, Green, Blue, White	<a href="#">54-202</a> , <a href="#">53-045</a> , <a href="#">40-639</a> , <a href="#">42-346</a> , <a href="#">42-347</a> , <a href="#">39-367</a> , <a href="#">39-368</a> , <a href="#">53-689</a> , <a href="#">53-692</a> , <a href="#">53-690</a> , <a href="#">53-693</a> , <a href="#">53-691</a> , <a href="#">53-694</a>
<a href="#">#66-307</a>	SugarCUBE™ Light Guide Adapter - 65	1.52	0.63	Red, Green, Blue, White	<a href="#">54-212</a>
<a href="#">#66-308</a>	SugarCUBE™ Light Guide Adapter - 66	1.52	0.565	Red, Green, Blue, White	<a href="#">54-210</a> , <a href="#">39-826</a> , <a href="#">58-839</a> , <a href="#">54-174</a> , <a href="#">38-659</a> , <a href="#">39-369</a> , <a href="#">39-370</a> , <a href="#">39-371</a>
<a href="#">#13-536</a>	SugarCUBE™ Light Guide Adapter - 3mm	0.57	0.314	Red, Green, Blue, White, Ultra White	<a href="#">54-202</a> , <a href="#">53-045</a> , <a href="#">40-639</a> , <a href="#">42-346</a> , <a href="#">42-347</a> , <a href="#">39-367</a> , <a href="#">39-368</a> , <a href="#">53-689</a> , <a href="#">53-692</a> , <a href="#">53-690</a> , <a href="#">53-693</a> , <a href="#">53-691</a> , <a href="#">53-694</a>  Ultra White MUST use liquid light guides
<a href="#">#13-537</a>	SugarCUBE™ Light Guide Adapter - 5mm	0.455	0.314	Red, Green, Blue, White, Ultra White	<a href="#">54-202</a> , <a href="#">53-045</a> , <a href="#">40-639</a> , <a href="#">42-346</a> , <a href="#">42-347</a> , <a href="#">39-367</a> , <a href="#">39-368</a> , <a href="#">53-689</a> , <a href="#">53-692</a> , <a href="#">53-690</a> , <a href="#">53-693</a> , <a href="#">53-691</a> , <a href="#">53-694</a>  Ultra White MUST use liquid light guides