

TECHSPEC®

S-Mount Iris Diaphragm Mount



TECHSPEC® S-Mount Iris Diaphragm Barrel

Stock #11-151 4 In Stock

-

1

+

₹15,037

ADD TO CART

Volume Pricing	
Qty 1-4	₹15,037 each
Qty 5-9	₹13,262 each
Qty 10-25	₹12,235 each
Need More?	Request Quote

Product Downloads

General

Iris Diaphragm

Function:

Physical & Mechanical Properties

12.0

Extension Length (mm):

15.0

Total Length (mm):

17.0	Outer Diameter (mm):
0.7 - 5.0	Clear Aperture CA (mm):
Threading & Mounting	
S-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Variable Apertures for C, S, and T-Mount Systems
 - Male and Female Thread at Opposite Ends for Easy Integration
 - Adjusted via Rotating Ring or Lever for Precision Control
- TECHSPEC® C, S, and T-Mount Iris Diaphragm Mounts feature iris diaphragms that allow for precision control over the internal aperture within a system. Using male and female threads, these mounts can be placed anywhere within a C, S, or T-Mount system. The apertures can be adjusted via a rotating ring for the C-Mount version, with a 4mm lever for the S-Mount version and with a 5mm lever for the T-Mount version. TECHSPEC C, S, and T-Mount Iris Diaphragm Mounts add 12mm, 12mm, and 18mm to the system length, respectively. These mounts are ideal for providing control over the f/#, field stop diameter, and overall energy throughput of a C, S, or T-Mount system.
- NOTE:** The iris planes sit approximately 15mm, 8mm, and 12mm from the female ends of the TECHSPEC C, S, and T-Mount Iris Diaphragm Mounts, respectively.

Technical Information

