

Schneider 28mm F-Mount Lens, Short WD



Stock **#87-107** [CONTACT US](#)

- 1 + **₹257,520.00**

ADD TO CART

Qty 1+
₹257,520.00

Volume Pricing
Request Quote

Get Product Downloads

Field of View @ Min Working Distance (mm):
449.00

Iris Option:
Variable

Length (mm):
88.50

Filter Thread:
M62.0 x0.75

Maximum Diameter (mm):
65.0

Weight (g): 523.00
Maximum Rear Protrusion (mm): 13.7
Maximum Image Circle (mm): 43.30
Horizontal Field of View, 35mm Sensor: 64°
Note: Optimized Working Distance: 233 - 833mm
Type: Fixed Focal Length Lens
Focal Length FL (mm): 28.00
Maximum Sensor Format: 35mm (43.3mm Image Circle)
Working Distance (mm): 0 - ∞
Mount: F-Mount
Aperture (f/#): f/2.8 - f/22
Distortion (%): <4.5
Coating: 400 - 1000 BBAR
Lens Wavelength Range: VIS-NIR Color Corrected

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant