



SCHOTT BG38, 12.5mm Dia., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-392** 10 TO 12 DAYS

[Additional Bandwidths](#)



1



₹3,567.00

ADD TO CART

Qty 1-10

₹3,567.00

Qty 11+

₹3,219.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
470.00

Density (g/cm³): 2.66
Glass/Filter Number: SCHOTT BG38
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.53
Surface Quality: 60-40
Transformation Temperature (°C): 482
Thickness (mm): 3.00 ±0.2
Type: Bandpass Filter
Wavelength: VIS
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--