

SCHOTT BG40, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT BG Glass (glass color will vary by product specification)

Stock **#16-900** 10 TO 12 DAYS

-

1

+

₹28,188.00

ADD TO CART

Qty 1-10
₹28,188.00
Qty 11+
₹25,230.00
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 165.0 x 165.0 +3.0/-0.0
Density (g/cm³): 2.74
Glass/Filter Number: SCHOTT BG40

Length (mm): 165.00
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.53
Transformation Temperature (°C): 313
Thickness (mm): 4.50 ±0.5
Type: Bandpass Filter
Wavelength: UV-VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Certificate of Conformance: View
--