

SCHOTT GG400, 50mm Sq., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-475** 10 TO 12 DAYS



1



₹6,743.00

ADD TO CART

Qty 1-10

₹6,743.00

Qty 11+

₹6,612.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Cut-On Wavelength (nm):
400.00 ±6

Density (g/cm³):

2.55
Glass/Filter Number: SCHOTT GG400
Length (mm): 50.00
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 480
Passband Limit 2 λ_{p2} (nm): 700
Index of Refraction n_d : 1.52
Spectral Transmittance t_p (%): 93
Stopband Limit λ_s (nm): 340
Surface Quality: 60-40
Transformation Temperature (°C): 537
Thickness (mm): 1.00 ±0.1
Type: Longpass Filter
Wavelength: VIS
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View