

SCHOTT KG2, 12.5mm Dia., 1mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#18-497** [CONTACT US](#)

- 1 + **₹2,697.00**

ADD TO CART

Qty 1-10
₹2,697.00
Qty 11+
₹2,436.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Density (g/cm³):
2.52

Glass/Filter Number:
[SCHOTT KG2](#)

Substrate: Heat Absorbing Glass
Operating Temperature (°C): 300 Maximum
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 605
Thickness (mm): 1.00 ±0.1
Type: IR Cut-Off Filter
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Wavelength Range (nm): 300 - 2700
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant