


SCHOTT NG11, 0.1 OD, 50mm Sq., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock #16-719 10 TO 12 DAYS

-

1

+

₹8,091.00

ADD TO CART

Qty 1-10

₹8,091.00

Qty 11+

₹7,134.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Optical Density OD (Average):
0.1 ±0.006 @ 546nm

Glass/Filter Number:
[SCHOTT NG11](#)

Length (mm):

50.00
Coating: Uncoated
Index of Refraction n_d: 1.50
Surface Quality: 80-50
Transformation Temperature (°C): 481
Thickness (mm): 0.60
Thickness Tolerance (mm): (nominal)
Transmission (%): 79.43 ±1.03% @ 546nm
Type: Neutral Density Filter
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.38
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
Reach 240: Compliant